

Feed Conductor Capability

FEED	PHASE LUG	NEUTRAL LUG	GROUND LUG (enclosure)	GROUND LUG (iso ground)
EF225 EF225G	300MCM 300MCM	300MCM 300MCM	2/0 2/0	N/A 1 AWG
EF250T5 EF250T5N EF250T5G EF250T5NG	300MCM 300MCM 300MCM 300MCM	300MCM 600MCM/(2)250MCM 300MCM 600MCM/(2)250MCM	2/0 2/0 2/0 2/0	N/A N/A 300MCM 300MCM
EF250T5L (large box) EF250T5NL (large box) EF250T5GL (large box) EF250T5NGL (large box)	600MCM/(2)250MCM 600MCM/(2)250MCM 600MCM/(2)250MCM 600MCM/(2)250MCM	600MCM/(2)250MCM 600MCM/(2)250MCM 600MCM/(2)250MCM 600MCM/(2)250MCM	2/0 2/0 2/0 2/0	N/A N/A 300MCM 300MCM
EF400T5 EF400T5N EF400T5G EF400T5NG	600MCM/(2)250MCM 600MCM/(2)250MCM 600MCM/(2)250MCM 600MCM/(2)250MCM	600MCM/(2)250MCM (2)600MCM 600MCM/(2)250MCM (2)600MCM	350MCM 350MCM 350MCM 350MCM	N/A N/A 300MCM 300MCM
EF800 (CC & CA) EF800G (CC & CA)	(2)600MCM (2)600MCM	(2)600MCM (2)600MCM	350MCM 350MCM	N/A 350MCM
TF225 CF225	350MCM 350MCM	350MCM 350MCM	2/0 2/0	N/A N/A
TF225G CF225G	350MCM 350MCM	350MCM 350MCM	2/0 2/0	1/0 1/0
TF250T5 TF250T5N TF250T5G TF250T5NG	600MCM/(2)250MCM 600MCM/(2)250MCM 600MCM/(2)250MCM 600MCM/(2)250MCM	600MCM/(2)250MCM 600MCM/(2)250MCM 600MCM/(2)250MCM 600MCM/(2)250MCM	2/0 2/0 2/0 2/0	N/A N/A 2/0 2/0
TF400T5 TF400T5N TF400T5G TF400T5NG	600MCM/(2)250MCM 600MCM/(2)250MCM 600MCM/(2)250MCM 600MCM/(2)250MCM	600MCM/(2)250MCM (2)600MCM 600MCM/(2)250MCM (2)600MCM	350MCM 350MCM 350MCM 350MCM	2/0 2/0
EF250T5G-4-FUSED EF400T5G-4-FUSED	500MCM (2)500MCM	300MCM 600MCM/(2)250MCM	2/0 350MCM	300MCM 300MCM